

**VERMOP**<sup>®</sup>  
PROFESSIONAL CLEANING SYSTEMS



**SPRINT V**

Floor cleaning

EN



## SPRINT SYSTEM

The new Generation Sprint V flat mop holder guarantees dual time saving for daily use. Your cleaning staff can attach mops faster than ever before; thanks to the holder's V shape, it slips smoothly into the pouches of the mop. A further benefit is that new staff do not have to be trained specially! The holder also contributes to greater square meter coverage in premises cleaning as it is particularly light and manoeuvrable and allows a speedy mopping process, even in heavily-furnished areas.

Furthermore, with the Sprint V holder, you are also investing into your staff's back health. The holder is opened via a hand switch while the operator remains in an upright position and the mop is discarded hygienically without having to be touched. Bending down to lift up dirty mops is no longer necessary!

Of course you can also have complete confidence in the cleaning performance of the Sprint V. The optimised contact surface of the holder ensures even mopping and very good dirt removal.

Combine the Sprint V with the versatile and durable VERMOP Sprint flat mop and the Scandic telescopic handle for the right working height.



# AT A GLANCE

## Simple attachment

Easy insertion of the holder into the pouches of the mop thanks to the V shape

## Ergonomic working

Hand-switch opening of the holder and mop discarding while standing upright

## Hygienic

No touching of soiled mops when discarding

## Spotless cleaning results

Optimum contact of the holder for very good dirt removal

## Fast, labour-saving work

Extremely manoeuvrable and smooth-running holder

## Areas of application

- General cleaning
- Disinfectant cleaning
- Wet cleaning
- High degree of soiling

## Site



Hospital / Nursing home • School / Nursery • Office / Administration • Industry

## Methods



F1 flat wringer • Vertical wringer VK 4 • Des tub • Pre-Wash • Dosing sieve • Dry cleaning • Spray method • Pour method



## VERMOP® INDIVIDUAL

Individual colour printing on mop, e.g. with your customer's logo, can be combined with colour-contrasting edge binding.

We would be pleased to sew RFID tags for our MopLog Medi-Tex control system, or for your own RFID logistic system, into our covers.



**Focus on ergonomics and healthy backs**

Around 4,000 times a year, the average cleaning operative bends over to lift a soiled mop off the floor. At the same time, back pain is the most frequent reason for medically-certified sick leave. It causes 7% of all lost working days.\* This is why, in developing cleaning equipment, VERMOP focuses closely on methods of use which are easy on the back. Optimise the working conditions of your staff with the Sprint V holder! It is opened via a finger switch while the user remains upright and the soiled mop is discarded without bending.

\*Source: Robert Koch-Institut (Hrsg) (2012) Rückenschmerzen. Gesundheitsberichterstattung des Bundes. Heft 53. RKI, Berlin (Robert Koch Institute (Ed) (2012) Back Pain. Government Health Report. Leaflet 53. RLK, Berlin )



**Very good cleaning performance**

The contact surface of the holder is optimised to achieve even mopping results and effective dirt removal.



**Dry pre-cleaning with cloth**

To facilitate pre-cleaning in order to remove loose dirt, fleece cloths can be wrapped around the holder and clipped on.



**Hygienic**

Soiled mops can be discarded without being touched.



**Manoeuvrable and fast**

Thanks to the highly mobile joint and the low weight, the holder moves easily around all kinds of obstacles.



**Comfortable attachment**

The equal-sided holder allows for the mop to be attached simply and quickly.



**Energy saving**

Combined with the Scandic telescopic handle with rotating ball, the holder glides over the floor with ease and minimum exertion.





**Suitable for all cleaning methods**


The Sprint V holder can be combined with all cleaning methods. Ideal for cleaning with pre-treated mops and attachment directly from the transport box.

**HOLDER**



**Sprint V Holder**

Description	code
40 cm, yellow	0049
50 cm, yellow	0059
pack. unit: 10	



**Sprint V Clip**

Description	code
Set, yellow	882705
pack. unit: 1   Application: Cloth cleaning	

**HANDLES**



**Scandic telescopic handle**

Description	code
with rotating ball, yellow	8903
pack. unit: 5   Dimensions: 1000 – 1700 mm, ø 23,5 mm   Sprint V / Twixter / Twix / Scandic Duo	



**telescopic handle**

Description	code
yellow	8923
pack. unit: 10   Dimensions: 900 – 1650 mm, ø 23,5 mm	



VERMOP Deutschland GmbH  
Kiesweg 4 – 6  
97877 Wertheim  
Germany  
Tel. + 49 9342 878 - 0  
Fax + 49 9342 878 - 173  
info@vermop.com  
www.vermop.com

SALMON-GROUP



We reserve the right to make technical changes and changes in content. No liability shall be assumed for errors or omissions. Printed on paper from sustainable sources.